

DEMAND
MORE

Hot water without the wait

Before Grundfos, hot water recirculation solutions were difficult, if not impossible. Now, installations in both new construction and existing homes are quick, easy and profitable.

Features & Benefits:

- Installations take an hour or less
- In retrofits, the Comfort System bypass valve makes it all possible with no return line and no need for electricity under the sink
- Uses less energy than a 25-watt light bulb (Comfort System Only)
- Can save up to 16,000 gallons of water per year
- Backed by a 30-month warranty
- All products certified to NSF-61 and NSF-372 standards

For more information, go to: grundfos.us



Comfort System

UP 15-10 SU7P TLC
Pump, valve, line-cord,
and (2) S.S. flex hoses.



COMFORT PM AUTO

UP 10-16 A PM BN5/LC
AUTOADAPT™ and line cord



ANSI/NSF61/372 and IAPMO listed

be
think
innovate

GRUNDFOS 

– Comfort System UP 15-10 SU7P TLC (Part# 595916)

Pump Technical Data:

Flow, Qmax 6.3 GPM (1.4 m³/h)
 Head, Hmax 5.1 ft (1.6 m)
 Motor: Single Phase, 115V
 Min. Fluid Temperature: 36°F (2°C)
 Max. Fluid Temperature: 150°F (66°C)
 Max. Working Pressure: 145 PSI

Electrical Data:


Volts: 1X115V
 Watts: 25W
 Amps: 0.23A

Electrical Connection: The pump is fitted with a 10ft. line-cord w/plug.

Timer: 3 control options available:

- Continuous
- 15-minute intervals
- OFF

Performance Curve:



– COMFORT PM Range


Pump Technical Data:

Flow, Qmax 2.2 GPM (0.5 m³/h)
 Head, Hmax 3.9 ft (1.2 m)
 Motor: Single Phase, 115V/208-230V
 Min. Fluid Temperature: 36°F (2°C)
 Max. Fluid Temperature: 203°F (95°C)
 Max. Working Pressure: 145 PSI
 Standard Features: 6ft. line-cord w/plug

Electrical Data:

Volts: 1X115V
 Watts: 5-8.5W
 Amps: 0.23A

Performance Curve:



Models	Part Number	1/2" Sweat	1/2" F FNPT	1 1/4" Union	Line Cord	Check Valve	Isolation Valve	AUTO
UP10-16 PM B5/LC	98420206	•			•			
UP10-16 PM BN5/LC	98420210		•		•			
UP10-16 A PM B5/LC	98420222	•			•			•
UP10-16 A PM BN5/LC	98420223		•		•			•
UP10-16 A PM BU/LC	98420224			•	•	•	•	•

L-UP-SL-024 Rev. 08-14

GRUNDFOS Kansas City
 17100 West 118th Terrace
 Olathe, Kansas 66061
 Phone: (913) 227-3400
 Fax: (913) 227-3500

GRUNDFOS Canada
 2941 Brighton Road
 Oakville, Ontario
 L6H 6C9
 Phone: (905) 829-9533
 Fax: (905) 829-9512

GRUNDFOS Mexico
 Boulevard TLC No. 15
 Parque Industrial Stiva Aeropuerto
 C.P. 66600 Apodaca, N.L. Mexico
 Phone: 011-52-81-8144 4000
 Fax: 011-52-81-8144 4010

www.grundfos.us

