



Dependable and durable jet pumps for supplying water to residential, agriculture or light commercial water transfer

– Grundfos JP jet pumps are a great choice for home and garden use

- Dual voltage motors 115/230 volts
- Full range of HP's
- Nozzle and Venturi clean out port
- Totally enclosed fan-cooled motors
- Quiet operation
- Available in cast iron and stainless steel models
- Built-in thermal overload for motor protection
- Self-priming and excellent suction lift
 - Up to 25 ft depth to water shallow well
 - Up to 90 ft depth to water deep well



**Old JPF Shallow Well
Cast-Iron Jet Pumps**

TYPE	HP	PH	VOLTS	PRESSURE SWITCH SETTING (PSI)	MATERIAL NUMBER
JPF3	1/2	1	115	30-50	96430412
JPF3	1/2	1	230	30-50	96430413
JPF4	3/4	1	115	30-50	96430414
JPF4	3/4	1	230	30-50	96430415
JPF5	1-1/2	1	230	50-70	96430416
JPF7	2	1	230	50-80	96457277

**New Shallow Well
Cast-Iron Jet Pumps**

TYPE	HP	PH	VOLTS	PRESSURE SWITCH SETTING (PSI)	MATERIAL NUMBER
JP05S-CI (JP4-47ASA)	1/2	1	115/230	30-50	97855073
JP07S-CI (JPA-54ASA)	3/4	1	115/230	30-50	97855081
JP10S-CI (JP4-61ASA)	1	1	115/230	30-50	97855085
JP15S-CI (JP5-61ASA)	1-1/2	1	230	40-60	97855091
JP20S-CI (JP8-62ASA)	2	1	230	40-60	97855094
JP30S-CI (JP12-51ASA)	3	1	230	40-60	97855095

**Old JPS Shallow Well
Stainless-Steel Jet Pumps**

TYPE	HP	PH	VOLTS	PRESSURE SWITCH SETTING (PSI)	MATERIAL NUMBER
JPS2	1/2	1	115	30-50	96430421
JPS2	1/2	1	230	30-50	96430422
JPS4	1	1	115	30-50	96430423
JPS4	1	1	230	30-50	96430424

**New Shallow Well
Stainless-Steel Jet Pumps**

TYPE	HP	PH	VOLTS	PRESSURE SWITCH SETTING (PSI)	MATERIAL NUMBER
JP05S-SS (JP4-47ASI)	1/2	1	115/230	30-50	97855075
JP07S-SS (JP4-54ASI)	3/4	1	115/230	30-50	97855083
JP10S-SS (JP4-61ASI)	1	1	115/230	30-50	97855088

**Old JDF Deep Well
Cast-Iron Jet Pumps***

TYPE	HP	PH	VOLTS	PRESSURE SWITCH SETTING (PSI)	MATERIAL NUMBER
JDF2	1/2	1	115	30-50	96430417
JDF2	1/2	1	230	30-50	96430418
JDF4	3/4	1	115	30-50	96430419
JDF4	3/4	1	230	30-50	96430420

**New Deep Well
Cast-Iron Jet Pumps***

TYPE	HP	PH	VOLTS	PRESSURE SWITCH SETTING (PSI)	MATERIAL NUMBER
JP05D-CI (JP4-47DSA)	1/2	1	115/230	30-50	97855072
JP07D-CI (JP4-54DSA)	3/4	1	115/230	30-50	97855080
JP15D-CI (JP5-61DSA)	1-1/2	1	230V	40-60	97855090
JP20D-CI (JP8-62DSA)	2	1	230V	40-60	97855093

*Ejector not included

*Ejector not included



**Deep Well Ejector for
JDF/JPF5/JPF7 Series**

TYPE	Material Number
E20 NPT	96654382
E25 NPT	96654383
E30 NPT	96654384



**Deep Well Ejector for
New Deep Well Series**

TYPE	Material Number
E20 NPT	96654382
E25 NPT	96654383
E30 NPT	96654384

L-JP-SL-002 REV. 06/12 (US)